



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #1-206138-0
CPC CABLE CLAMPS



TE Part #1546413-3
ETHERNET RJ-45 BLKHD PASSTHRU



TE Part #1-66105-8
III+ SKT,24-20,30AU/FL,SMPACK



TE Part #1-770967-1
03P MINI UMNL R/A HDR ASSY AU



TE Part #1-66103-7
III+ PIN, 24-20, 15AU/FL, SMPACK

TE Part #1623927-4
CFR16 5% 10K

TE Part #102312-1
Universal Headers: Ejector Latch

TE Part #YDTS26W13-08SAV001
D38999: Straight Plug, 13-08 Insert

TE Part #193990-2
SKT ASSY, TYPE XII, #8 AWG

TE Part #1437535-7
DIP Socket: Standard, Stamped & Formed, Closed, Gold

Documents

Product Drawings

508-AG11D-LF=500 DIP,PCB,AU/SN

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1571550-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-1571550-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1571550-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

DIP Sockets Quick Reference Guide (EN)

English

Product Environmental Compliance

TE Material Declaration

English