



## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2019 (201) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

### Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Customers Also Bought

 <p>TE Part #2-100103-6 Latch Connector: Strain Relief</p>	 <p>TE Part #1393788-3 AXICOM P2 STANDARD</p>	 <p>TE Part #1-1740194-2 D-Sub Receptacle Assy: Eurostyle, Right Angle, Surface Mount, 2.74mm</p>	 <p>TE Part #1658694-5 AMP-LATCH UNIVERSAL HEADERS</p>
---	---	--	---



TE Part #2-215882-6  
26 WAY GREY MK II RECP



TE Part #1734839-6  
0.5mm FPC Connectors



TE Part #1734346-1  
STD USB TYPE B, R/A, SMT



TE Part #640457-2  
Polyester Right Angle PCB Header:  
2.54mm, Unshrouded, MTA 100



TE Part #227161-7  
BNC Right Angle M Jack RF  
Connector, 50 Ohm, Bayonet  
Coupling Mechanism



TE Part #1337771-1  
50 OHM COAX BNC STR PLUG STR P