

RNF-100-3/64-BK-SP ✓ ACTIVE

Raychem RNF-100

TE Internal #: 5052844058

TE Internal Description: RNF-100-3/64-BK-SP

Mil-Spec: [M23053/5-101-0]

[View on TE.com >](#)



Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | [Raychem RNF-100](#)



Heat Shrink Tubing(672)



Power Cable Tubing & Accessories(8)

Customers Also Bought



TE Part #2-320563-2
PIDG RING TONGUE TERMINALS



TE Part #1734709-2
AMP HPI 1.0MM HEADERS



TE Part #296977-000
Low Profile Heat Shrink Boots: Poly
Mold, Lipped, Right Angle



TE Part #323152
DG 22-16COM 22-18MIL HR R 8



TE Part #1393771-7
JWD-171-10=REED RELAYS



TE Part #1-487937-0
FFC Receptacle Housing: 1.27mm



TE Part #CV4186-000
RNF-100-1/4-BK-SP-SH



TE Part #181953-1
250 FASTON, TAB, BR



TE Part #398741-000
TMS-9.5-9



TE Part #1437294-4
106-8859-00="F/S JMPR NMX .100

Documents

Datasheets & Catalog Pages

[RNF-100 Pages from 9-1773447-9](#)

English

Application Tooling for Raychem Heat Shrink Product

English

Product Specifications

Quality Specification

English

RNF-100-3/64-BK-SP

RNF-100-3/64-BK-SP
Mil-Spec: [M23053/5-101-0]

