

RNF-100-1/16-0-SP ✓ ACTIVE

Raychem RNF-100

TE Internal #: 5052894048

TE Internal Description: RNF-100-1/16-0-SP

RNF-3000 Single Wall Stick Heat Shrink

[View on TE.com >](#)



[All RNF-3000 Single Wall Stick Heat Shrink \(180\)](#)

Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | [Raychem RNF-100](#)



Heat Shrink Tubing(672)



Power Cable Tubing & Accessories(8)

Customers Also Bought



TE Part #2-794615-0
PANEL MT DBL ROW HSG 20 POS



TE Part #1-1718624-1
AMP MCP, SEALED CONNECTOR HOUSING




TE Part #1-1718484-4
AMP MCP BACKSHELLS



TE Part #1011-331-0205
DEUTSCH DT BACKSHELLS



TE Part #1452503-2
MCON, RECEPTACLE AND TAB



TE Part #153211-1
3 M/M LANCED SOCKET



TE Part #2177526-2
CABLE INSERT TOOL,25qmm



TE Part #ZPF00000000018132
FDPA 50-14-19 PN-K-A5610



TE Part #2141810-2
SHIELDING SLEEVE



TE Part #2303288-1
60POS,MCON 1.2,REC HSG ASSY,SLD, COD A

Documents

Datasheets & Catalog Pages

[RNF-100 Pages from 9-1773447-9](#)

English

Application Tooling for Raychem Heat Shrink Product

English

Flexible, Flame-Retardant, High Performance, Polyolefin Heat-Shrinkable Tubing

English



Product Specifications

Quality Specification

English

Product Environmental Compliance

Safety Datasheet

Safety Datasheet

German

Safety Datasheet

English

Safety Datasheet

English

Safety Datasheet

English

Safety Datasheet

English

Safety Datasheet

Safety Datasheet

Safety Datasheet

French

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet