


5390195-6 × OBSOLETE

AMP-METRIMATE

TE Internal #: 5390195-6

TE Internal Description: SKT,DIMM IIP,168,L/P,NB DRAM,PB-FREE

[View on TE.com >](#)



Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | AMP-METRIMATE



Card Edge Power Connectors(1)



Card Guide Hardware(1)



Portable Crimp Tools(1)



Rack & Panel Connectors(1)



Rectangular Power Connectors(9)



RF Connectors(1)



RJ45 Connectors(45)



SO DIMM Sockets(14)



Wire-to-Board Headers & Receptacles (3)

Customers Also Bought



TE Part #2118721-4
STD SHIELD COVER, AL-38.60X25.90X2.00MM



TE Part #413194-1
BNC RF Connector: Male (Jack), Right-angle, 75 Ohm




TE Part #2289129-3
ZQSFP+ CAGE& CONN 2X2, EMI SPRING, 4 LP



TE Part #5748989-1
D-Sub Receptacle Assembly: Right Angle, Shell Size 3, 2.77mm



TE Part #1-5353727-0
.6FHP08H,280,B,GIG,08/Sn,ST,NSYes



TE Part #1-5353729-0
.6FHR04H,280,B,GIG,08/Sn,ST,NSYes



TE Part #2085958-1
ICCON,SIZE 4,LOCKING PIN ASSEMBLY



TE Part #5767025-1
MICTOR .707 PLUG ASSY, 38 POS.



TE Part #NB19382001
RNF-100-1/8-YO-STK



TE Part #5-2287906-1
FAKRA, 1 POS, EDGE MOUNT, 12 OCLOCK ASSY

Documents



CAD Files

3D PDF

English

Customer View Model

[ENG_CVM_5390195-6_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_5390195-6_B.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_5390195-6_B.2d_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.