



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.



Compatible Parts



 TE Part # 1-5221128-0 PLUG,COMMERCIAL BNC	 TE Part # 1-221128-0 PLUG,COMMERCIAL BNC	 TE Part # 1-5221128-1 PLUG,COMMERCIAL BNC	 TE Part # 2-5221128-7 PLUG,COMMERCIAL BNC
 TE Part # 5221128-1 PLUG,COMMERCIAL BNC	 TE Part # 5413771-1 JACK BLKHD,COML BNC,HEX CRIMP	 TE Part # 221128-1 PLUG,COMMERCIAL BNC	 TE Part # 1-5221128-7 PLUG,COMMERCIAL BNC
 TE Part # CAT-076-TNCF50 TNC Connector: Female (Plug), 50 Ohm	 TE Part # 2-221128-7 PLUG,COMMERCIAL BNC	 TE Part # 5413959-6 BNC HEX RT ANG PLUG 50 OHM	 TE Part # 1-221128-1 PLUG,COMMERCIAL BNC
 TE Part # 1-221128-7 PLUG,COMMERCIAL BNC	 TE Part # 1-221128-8 PLUG,DUAL CRIMP,COMMERCIAL, BNC	 TE Part # 221128-2 PLUG,COMMERCIAL BNC	 TE Part # 3-221128-1 PLUG, COMMERCIAL BNC
 TE Part # 5221128-2 PLUG,COMMERCIAL BNC	 TE Part # 5413959-8 PLUG,RTANG,50 OHM,COML BNC		

Customers Also Bought



 TE Part #1879074-4 Power Resistor: Aluminum Housed, 75 Watt	 TE Part #2-5221128-1 PLUG,COMMERCIAL BNC	 TE Part #3-644460-2 02P MTA156 CONN ASSY 18AWG ORA	 TE Part #225532-1 SMA PLUG FLEX
 TE Part #3-1437504-3 8080-1G15=TRANSISTOR SOCKET AS	 TE Part #1-2176217-3 CPF A 0805 39R 0.1% 25PPM 1K RL	 TE Part #YDTS20W21-39PN0000 D38999: Square Flange, 21-39 insert	 TE Part #3-1579001-9 ERGO DIE MCP 1,2 CB
 TE Part #2-1618241-8 K81B235=RELAY, VACUUM, SPST-NC	 TE Part #318450-1 PROCRIMP HT & DIE, BNC, TNC		

Documents

Datasheets & Catalog Pages

1-1773865-2_1015_Commercial Manual Hand Tools

English

Instruction Sheets

Instruction Sheet (U.S.)

English