



Sensors > Position Sensors > Angular Position Sensors - Hollow Shaft Resolvers



Resolver Size: 21

Pole Pairs: 1

Angular Error: 12'

Features

Configuration Features

Resolver Size	21
Pole Pairs	1

Other

Angular Error	12'
---------------	-----

Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 40-0986-000-000
623 INSULATION INSERT, 12-PIN



TE Part # 61-0171-080-026
BANDOLEER CONTACT PIN 1MM,
400 PCS ROL

Customers Also Bought



TE Part #1393260-7
Forced Guided Relay, Reinforced
Insulate



TE Part #1-1579007-6
EXTRACTION TOOL



TE Part #1393230-7
RP3SL005



TE Part #1419108-1
RT114012



TE Part #1-2132230-5
EP2.5 Shrouded HDR ASSY 15P VE



TE Part #1393212-8
PCB Power Relay: 40 Amp, Monostable



TE Part #1623728-8
Wirewound Resistor: Vertical Mount



TE Part #1-1393763-6
V23100V4024A 10



Documents

Product Drawings

[RESOLVER V23401-U1016-B110](#)

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_6-1393048-1_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6-1393048-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6-1393048-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[6-1393048-1 data sheet](#)

English