



## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # CJ2087-000  
[HL2010E-KIT-120V](#)

## Customers Also Bought



TE Part #1393793-9  
AXICOM D2N SENSITIVE



TE Part #615970-001  
F-23-FR



TE Part #193578-001  
T14-23FR



TE Part #1546670-8  
8P .437\" DR BARRIER,W/BND SCRW



TE Part #207757-000  
55A1823-20-9/96-9CS2275



TE Part #5509122113  
Dual Wall Heat Shrink Tubing: Stick



TE Part #YDTS26F25-61SAV001  
D38999: Straight Plug, 25-61 Insert



TE Part #282220-000  
81044/12-16-0



TE Part #1532207-2  
M83513/02-GC, MCKS-C2-B-51SS



TE Part #271817-000  
55A1151-24-MST5-9CS2275

## Documents

### Product Drawings

[222F221-51-0-CS5410](#)

English

### Product Specifications

[Product Specification](#)

English