



## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # CAT-AM7017-C7671  
AMP COMMON TERMINATION CONTACTS

TE Part # 175102-4  
AMP CT CRIMP REC WITH NOTCH

TE Part # 175102-2  
CRIMP TYPE RECEPT.CONTACT

TE Part # 175102-3  
AMP CT CONN 2.0 CONT (#26-#22)

## Customers Also Bought



TE Part #352068-1  
HM Receptacle Connector: Traditional Backplane, Coplanar, 2mm



TE Part #1-175102-1  
AMP COMMON TERMINATION CONTACTS



TE Part #767054-1  
MICT, RECPT, 38, ASSY, PDNI



TE Part #103906-3  
04 MTE HDR SRRA LATCH .100CL



TE Part #103638-1  
02 MTE HDR SRST LATCH .100CL



TE Part #103906-5  
06 MTE HDR SRRA LATCH .100CL



TE Part #1-745968-4  
D-Sub Plug Assembly: Vertical, Shell Size 3, 2.74mm



TE Part #103635-2  
03 MTE HDR SRRA LATCH .100CL



TE Part #102320-1  
Universal Headers: Ejector Latch



TE Part #1-770166-1  
02P MINI UMNL ASSY VO SNAU LF

## Documents

### Product Drawings

PISTOL GRIP H/T FOR CT CRIMP

English

### Datasheets & Catalog Pages

#### Bottoming Dies

English

### Instruction Sheets

Instruction Sheet (non U.S.)



English

**PISTOL GRIP HAND TOOL FOR CT RECEPTACLE CONTACT**

English