

AD-1480-748-SOLDTK-HOLDER

✓ ACTIVE

TE Internal #: 994040-000

TE Internal Description: AD-1480

[View on TE.com >](#)



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought

TE Part #38941-20L  
CONT PIN

TE Part #576784  
HHHT PIDG PEEK STRATO 10 ASSY

TE Part #58514-1  
PROCrimp TL W/DIE MR26-18

TE Part #207241-1  
CABLE BOOT, SZ 17, CPC





TE Part #207387-1  
CABLE GRIP,SZ 17,CPC



TE Part #59239-4  
HHHT PIDG PG 12-10 ASSY



TE Part #2063857-1  
CCII .058 DIA REC CONT 24-18 ASSY

TE Part #512809-000  
AD-1569-1-SOLDERTACT-HLDR



TE Part #994057-000  
AD-1494-723-SLTC-HLD-ASY

TE Part #605837-ZZ  
TOOL INS-REM

Documents

Product Drawings

AD-1480

English

Product Specifications

Termination Procedure for 748 Series SolderTacts Contacts for Twisted Pair Cable D-602-0126, D-602-0127

English