



WP

TE Internal #: A77951-000

TE Internal Description: WP-064064-25-9

WP WHITE POLYESTER LABELS

[View on TE.com >](#)



All WP WHITE POLYESTER LABELS (29)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2186500-1  
T3212-PRINTER

TE Part # 1-2186502-1  
T3224-PRINTER

TE Part # 1-2186503-1  
T3224-SWARE-PRINTER

TE Part # 1-2186501-1  
T3212-SWARE-PRINTER

Also in the Series | WP

Standard Labels(29)

Customers Also Bought

TE Part #1-640456-0  
Polyester Vertical PCB Header: 2.54 mm, Unshrouded, No Mating Alignment

TE Part #2-84953-8  
1MM FPC HORZ.TOP CONT.ASSY 28P

TE Part #1-1825059-3  
ADF04S04=DIP SWT,FLUSH,SMT-GW

TE Part #2-323930-2  
TERMASHIELD, SN, VIOLET, .033-

TE Part #2106003-2  
Connector, SMT-IDC, 2 position, 18AWG

TE Part #4-2176245-8  
CRGS1206 5% 8K2

TE Part #2176338-1  
CRGCQ 0402 1R0 5%

TE Part #1623696-1  
CRG2512 1% 100R

TE Part #280523-2  
12P MODU II SHRD HDR,RT ANG 0.38 AU

TE Part #F05902-000  
EP-762254-5-9



Documents

Product Drawings

WP-064064-25-9

English

Datasheets & Catalog Pages

WP White Polyester labels

English

IDENTIFICATION SELECTION GUIDE

English