



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | [Neohm CFR](#)




Through-Hole Resistors(337)


Customers Also Bought




TE Part #1-2314102-1
M12 CRIMP CONTACT FOR D AND A5



TE Part #5-1630186-7
Power Resistors: Aluminum Housed, HSA



TE Part #2351885-2
2POS TB HDR 180 DEG, PITCH 5.0&TL 4.5mm



TE Part #2176399-8
3502 1K0 5%



TE Part #3-2176348-9
CRGCQ 2010 2M2 5%



TE Part #9-2176378-0
RQ 0805 84R5 0.1% 10PPM 5K RL



TE Part #2-1415899-0
PCB Power Relay: 12-16 Amp, Monostable



TE Part #641643-2
Connector Contact: Socket /Receptacle, Wire-to-Board / Wire-to-Wire, MTA 100



TE Part #8-35216-1
PIDG SLOTTED RING TONGUE TERMINALS



TE Part #C145614001
VERSAFLEX-03-0-SP

Documents

Product Drawings

CFR25 5% 82K

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_7-1623931-8_BA.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_7-1623931-8_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_7-1623931-8_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1309350_PASSIVE_COMPONENT](#)

English

[Ceramic Film Fixed Resistors - Type CFR Series - Tyco Electronics Passives](#)

English