

VOLTMETER WITH 3 DIGIT LED DISPLAY

COM-VM330



This small mini voltmeter for voltages from 3 to 30 V has a 3 digit 7-segment display (0.36 Inch). The measured value can be displayed with 1 or 2 decimal digits and is refreshed every 0.3 seconds. This measurement device is outstanding by its very low power consumption of less than 30 mA and can be mounted using the 2 mounting holes.

MAIN FEATURES

Model	VM330
Special features	power supply via measurement voltage
Display	0.36 inch LED 7-segment display, shows 1 or 2 decimal digits
Dimensions	33 x 14.5 x 9.5 mm
Items delivered	DVC mini voltmeter with 2 wires each 18 cm

FURTHER SPECIFICATIONS

Operating voltage	3 V (via measurement voltage)
Measurement voltage	3 - 30 V
Measurement accuracy	0.1 %
Current consumption	< 30 mA
refresh rate	approx. 300 ms
input resistance	> 100 kΩ
voltage protection	Reverse polarity protection
Environment temperature	-10 - 65°C

FURTHER DETAILS

Article No.	COM-VM330
EAN:	4250236821955
Customs Tariff No.	8473302000

