


NOTE:

1. 100% OPEN SHORT, MISS WIRE TEST
2. FLUKE CHANNEL LINK TEST
3. PRINT WORD:
CAT6A S/FTP 4x2x26AWG/7 LSZH ISO/IEC11801 & EN50173 & ANSI/TIA568C.2
4. ROHS 3.0 AND REACH COMPLIANT
5. Operating Temperature: -20 ° C ~ +75° C
Storage temperature: -20°C ~ +75°C
OPERATION HUMIDITY: 30% ~ 85%
Storage humidity: 10% ~ 85%
6. PACKING: Bandrole with Euro hole w/RENKFORCE sticker

WIRING DIAGRAM



MATERIAL LIST

③	OVER MOLD	85A PVC	2	
②	CONNECTOR	RJ45 8P8C'S SHIELDED THE SHELL PLATED NICKEL, PIN GOLD PLATED 3u", TRANSPARENT Blue	2	
①	CABLE	CAT. 6A S/FTP 26AWG(BC+AL-FOIL)*4P+Braid(AL-MG) JACKET:LSZH/IEC60332-1-2, OD:6.0±0.2mm	1	
NO.	PARTS NAME	SPECIFICATION STANDARD	QT'Y	REMARK
		NEW		2021-09-06
BY	CHK	REVISION RECORD MODIFICATION	DATE	REV.

CUSTOMER	CN	ITEM NO.	SEE THE CHART
PRODUCT NAME	CAT.6A S/FTP 90° to 90° PATCH CORD	UNO ITEM NO.	AA217312
DRAWN BY	CHECK BY	APPO BY	DATE
Arvin	Alvan		2021-09-06

CHART:

COLOR: Grey (RAL7035)	
ITEM NO.	Length
2446234	150 ± 10
2446235	250 ± 10
2446236	500 ± 15
2446237	1000 ± 20
2446238	2000 ± 30
2446239	3000 ± 50
2446240	5000 ± 100
2446241	10000 ± 200
2446259	15000 ± 300
2446260	20000 ± 300
2446261	30000 ± 300

CUSTOMER		CN		ITEM NO.		SEE THE CHART			
PRODUCT NAME		CAT. 6A S/FTP 90° to 90° PATCH CORD		UNO ITEM NO.		AA217312		UNIT	MM
NEW		2021-09-06		A		DRAWN BY		CHECK BY	
BY		CHK		REVISION RECORD MODIFICATION		DATE		REV.	
				Arvin		Alvan		2021-09-06	