

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0002081001](#)
Status: **Active**
Overview: [MLX Power Connectors](#)
Description: MLX Female Crimp Terminal 42024, 14-20 AWG, Reel, Brass, Tin (Sn) Plating

Documents:

Drawing (PDF)	Datasheet (PDF)
Product Specification PS-42022-0001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Test Summary TS-42022-0001-001 (PDF)	

General

Product Family	Crimp Terminals
Series	42024
Application	Power, Wire-to-Board, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	MLX Power Connectors
Packaging Alternative	02081002 (Loose)
Product Name	MLX
UPC	800753615878

Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.406/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.52-3.30mm
Wire Size AWG	14, 16, 18, 20
Wire Size mm ²	N/A

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	42024-1A1
--------------------	-----------

Reference - Drawing Numbers

Product Specification	PS-42022-0001-001
Sales Drawing	SD-42024-XXXX-001
Test Summary	TS-42022-0001-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[42024 Series](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool for MLX 2.13mm Diameter Pin and Socket Crimp Terminals	11010168
PremiumGrade Hand Crimp Tool for MLX Pin and Socket Terminals, 14-20 AWG	638116800
FineAdjust Applicator for Crimp Terminals, 14-20 AWG Wire	639007500

with 2.08-2.50mm
Diameter Insulation
FineAdjust Applicator 639009800
for Crimp Terminals,
14-20 AWG Wire
with 2.65-3.30mm
Diameter Insulation
FineAdjust Applicator 639009900
for Crimp Terminals,
14-20 AWG Wire
with 2.41-2.95mm
Diameter Insulation
T2 Terminator 639107500
for MLX Crimp
Terminals, 14-20
AWG
T2 Terminator 639109800
Tooling Die for Crimp
Terminals, 14-20
AWG Wire
T2 Terminator 639109900
Tooling Die for Crimp
Terminals, 14-20
AWG Wire

This document was generated on 08/17/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION