

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0008650105

Status:

Active

Overview:

Description:

KK 254 Crimp Terminal 8088, 22-30 AWG, Gold/Nickel, Reel

General	
Product Family	Crimp Terminals
Series	8088
Application	Signal
Crimp Quality Equipment	Yes
Overview	kk_interconnect_solutions
Product Name	KK 254
UPC	800753745810
Physical	
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Nickel
Net Weight	0.071/g
Packaging Type	Reel
Plating min - Mating	0.381µm
Plating min - Termination	0.762µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.57mm max.
Wire Size AWG	22, 24, 26, 28, 30
Wire Size mm²	N/A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	8088-(555)
Reference - Drawing Numbers	
Product Specification	PS-99020-0088-001
Sales Drawing	SD-8088-XXXX-001

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

8088 Series

Use With

2695 , 6471

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extraction Tool for KK 2.54mm Terminals, 22-30 AWG	11030022
Terminator Die	11402102
Insertion Tool for KK 2.54mm Terminals, 22-30 AWG	638120000
Mini-Mac Applicator for KK and Anti-Fish Hook Terminals for 22-30 AWG Wire with Insulation Diameter 1.12-1.57mm	638887100

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION