

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0008700103**  
**Status:** **Active**  
**Overview:** Mini-Latch Wire-to-Board / Wire-to-Wire Connector System  
**Description:** 2.50mm Pitch Mini-Latch Crimp Terminal, Male, Brass, Bag

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification PS-51191-003-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification SPK-5241-001-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Crimp Terminals
Series	<a href="#">5241</a>
Application	Signal, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	<a href="#">Mini-Latch Wire-to-Board / Wire-to-Wire Connector System</a>
Packaging Alternative	<a href="#">08700102 (Reel)</a>
Product Name	Mini-Latch
UPC	800753534858

**Physical**

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	65.400/mg
Packaging Type	Bag
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.15-1.90mm
Wire Size AWG	22, 24, 26, 28
Wire Size mm <sup>2</sup>	N/A

**Electrical**

Current - Maximum per Contact	3.0A
-------------------------------	------

**Material Info**

Engineering Number	5241TL
--------------------	--------

**Reference - Drawing Numbers**

Packaging Specification	SPK-5241-001-001
Product Specification	PS-51191-003-001
Sales Drawing	SD-5241X-001



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[5241 Series](#)

**Use With**

[5240](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

<b>Description</b>	<b>Product #</b>
--------------------	------------------

PremiumGrade Hand	<a href="#">638190800</a>
Crimp Tool for Mini-Fit Jr. Male and Female Terminals, 22-28 AWG	

**Japan**

<b>Description</b>	<b>Product #</b>
--------------------	------------------

Hand Extraction Tool	<a href="#">11260060</a>
----------------------	--------------------------

This document was generated on 08/04/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**