This document was generated on 08/16/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0009501051
Status: Active
Overview: SPOX Connector System
Description: 3.96mm Pitch SPOX Crimp Housing, Female, with Friction Ramp, 5 Circuits, Natural



Series image - Reference only

Documents:

- 3D Model
- 3D Model (PDF)
- Drawing (PDF)
- Product Specification PS-5195-003-001 (PDF)
- Product Specification PS-5195-005-001 (PDF)
- Product Specification PS-5273-003-001 (PDF)
- Product Specification PS-5273-004-001 (PDF)
- RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	5195
Application	Signal, Wire-to-Board
Overview	SPOX Connector System
Product Name	SPOX
UPC	800753534445
Physical	
Circuits (maximum)	5
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	1467.100/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Pitch - Termination Interface	3.96mm
Stackable	No
Temperature Range - Operating	-40° to +105°C
Material Info	
Engineering Number	5195-05
Reference - Drawing Numbers	
Product Specification	PS-5195-003-001, PS-5195-005-001, PS-5273-003-001, PS-5273-004-001
Sales Drawing	SD-5195-N-020

EU ELV
Not Relevant

EU RoHS | **China RoHS**
Compliant

REACH SVHC
Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free Status
Low-Halogen

For more information, please visit Contact US

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
5195 Series

Mates With
5272 , 5273 , 5274 , 5096 , 53405 , 5271

Use With
5194

This document was generated on 08/16/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION