

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0009508021](#)
Status: **Active**
Overview: [KK Interconnect Solutions](#)
Description: KK 3.96mm Crimp Terminal Housing, Friction Ramp, 2 Circuits, Natural

Documents:

[3D Model](#) [Product Specification PS-08-50-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Crimp Housings
 Series [41695](#)
 Application Power, Wire-to-Board
 Overview [KK Interconnect Solutions](#)
 Product Name KK 396
 UPC 800753613775

Physical

Breakaway No
 Circuits (maximum) 2
 Color - Resin Natural
 Flammability 94V-0
 Gender Receptacle
 Glow-Wire Capable No
 Keying to Mating Part None
 Lock to Mating Part Yes
 Material - Resin Polyester
 Net Weight 0.719/g
 Number of Rows 1
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface 3.96mm
 Temperature Range - Operating See Product Specification

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Engineering Number 41695-N-B2

Reference - Drawing Numbers

Product Specification PS-08-50-001
 Sales Drawing SD-41695-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2020)9139-DC (19
 Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[41695 Series](#)

Mates With

KK 396 Header [41791](#) , [41792](#) , [41671](#) ,
[41672](#) , [41661](#) , [41662](#)

Use With

KK 396 Crimp Terminals [2478](#) , [2578](#) , [6838](#)
 , [7258](#) , [45570](#)
L1NK 396 Pre-Crimped
 Lead [797582145](#) , [797582146](#)