

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0010013026](#)
Status: **Active**
Overview: [SPOX Connector System](#)
Description: 5.08mm Pitch SPOX Crimp Terminal Housing, 2 Circuits, Natural

Documents:
[3D Model](#) [Product Specification PS-5197-001-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family Crimp Housings
Series [5197](#)
Application Signal, Wire-to-Board
Overview [SPOX Connector System](#)
Product Name SPOX
UPC 800753612631

Physical

Circuits (maximum) 2
Color - Resin Natural
Flammability 94V-2
Gender Receptacle
Glow-Wire Capable No
Material - Resin Nylon
Net Weight 766.600/mg
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 5.08mm
Stackable No
Temperature Range - Operating -40° to +105°C

Material Info

Engineering Number 5197-02

Reference - Drawing Numbers

Product Specification PS-5197-001-001
Sales Drawing SD-5197-N-020



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[5197](#) Series

Mates With

[5281](#) , [5282](#)

Use With

[5194](#) , [5225](#)