

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0011030043

Status:

Active

Overview:

Application Tooling

Description:

Extraction Tool for Micro-Fit Terminals

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207121
Function	Extraction
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	N/A
Tool Type	Extraction Hand Tool
UPC	800754211260
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number

HT60923A

Reference - Drawing Numbers

Application Tooling Documents

ATS-011030043-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Missing Compliance Data	
REACH SVHC	
Missing Compliance Data	
Halogen-Free Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207121 Series

Application Tooling Description	FAQ Product #
Micro-Fit High-Current RMF Crimp Terminal, Female, 2.540µm Bright Tin Plating, 18 AWG	2039510001
Micro-Fit+ Crimp Terminal, Female, Tin (Sn) Plating, 26-30 AWG	2064600011
Micro-Fit+ Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 26-30 AWG	2064600012
Micro-Fit+ Crimp Terminal, Female, 0.75µm Gold (Au) Plating, 26-30 AWG	2064600013
Micro-Fit+ Crimp Terminal, Female,	2064600021

	Tin (Sn) Plating, 20-24 AWG	
	Micro-Fit+ Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 20-24 AWG	<u>2064600022</u>
	Micro-Fit+ Crimp Terminal, Female, 0.75µm Gold (Au) Plating, 20-24 AWG	<u>2064600023</u>
	Micro-Fit+ Crimp Terminal, Female, Tin (Sn) Plating, 18 AWG	<u>2064600031</u>
	Micro-Fit+ Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 18 AWG	<u>2064600032</u>
	Micro-Fit+ Crimp Terminal, Female, 0.75µm Gold (Au) Plating, 18 AWG	<u>2064600033</u>
	Micro-Fit+ Crimp Terminal, Female, Tin (Sn) Plating, 16 AWG	<u>2064600041</u>
	Micro-Fit+ Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 16 AWG	<u>2064600042</u>
	Micro-Fit+ Crimp Terminal, Female, 0.75µm Gold (Au) Plating, 16 AWG	<u>2064600043</u>
	Micro-Fit 3.0 Crimp Terminal, Female, with Tin (Sn) Plated Phosphor Bronze Contact, 20-24 AWG, Reel	<u>430300001</u>
	Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 20-24 AWG, Reel	<u>430300002</u>
	Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 20-24 AWG, Reel	<u>430300003</u>
	Micro-Fit 3.0 Crimp Terminal, Female, with Tin (Sn) Plated Phosphor Bronze Contact, 26-30 AWG, Reel	<u>430300004</u>
	Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 26-30 AWG, Reel	<u>430300005</u>

	Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 26-30 AWG, Reel	430300006
	Micro-Fit 3.0 Crimp Terminal, Female, with Tin (Sn) Plated Phosphor Bronze Contact, 20-24 AWG, Bag	430300007
	Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 20-24 AWG, Bag	430300008
	Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 20-24 AWG, Bag	430300009
	Micro-Fit 3.0 Crimp Terminal, Female, with Tin (Sn) Plated Phosphor Bronze Contact, 26-30 AWG, Bag	430300010
	Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 26-30 AWG, Bag	430300011
	Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 26-30 AWG, Bag	430300012
	Micro-Fit 3.0 Crimp Terminal, Female, with Tin (Sn) Plated Phosphor Bronze Contact, 18 AWG, .073in / 1.85mm Max Insulation Outside Diameter, Reel	430300038
	Micro-Fit 3.0 Crimp Terminal, Female, with 0.38µm Select Gold (Au) Plated Phosphor Bronze Contact, 18 AWG, .073in / 1.85mm Max Insulation Outside Diameter, Reel	430300039
	Micro-Fit 3.0 Crimp Terminal, Female, with 0.76µm Select Gold (Au)	430300040

Plated Phosphor
Bronze Contact,
18 AWG, .073in /
1.85mm Max
Insulation Outside
Diameter, Reel
Micro-Fit 3.0 Crimp [430310001](#)
Terminal, Male,
with Tin (Sn) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Reel
Micro-Fit 3.0 Crimp [430310002](#)
Terminal, Male,
with 0.38µm Select
Gold (Au) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Reel
Micro-Fit 3.0 Crimp [430310003](#)
Terminal, Male,
with 0.76µm Select
Gold (Au) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Reel
Micro-Fit 3.0 Crimp [430310004](#)
Terminal, Male,
with Tin (Sn) Plated
Phosphor Bronze
Contact, 26-30 AWG,
Reel
Micro-Fit 3.0 Crimp [430310005](#)
Terminal, Male,
with 0.38µm Select
Gold (Au) Plated
Phosphor Bronze
Contact, 26-30 AWG,
Reel
Micro-Fit 3.0 Crimp [430310006](#)
Terminal, Male,
with 0.76µm Select
Gold (Au) Plated
Phosphor Bronze
Contact, 26-30 AWG,
Reel
Micro-Fit 3.0 Crimp [430310007](#)
Terminal, Male,
with Tin (Sn) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Bag
Micro-Fit 3.0 Crimp [430310008](#)
Terminal, Male,
with 0.38µm Select
Gold (Au) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Bag
Micro-Fit 3.0 Crimp [430310009](#)
Terminal, Male,
with 0.76µm Select
Gold (Au) Plated
Phosphor Bronze

Contact, 20-24 AWG,
Bag
Micro-Fit 3.0 Crimp [430310010](#)
Terminal, Male,
with Tin (Sn) Plated
Phosphor Bronze
Contact, 26-30 AWG,
Bag
Micro-Fit 3.0 Crimp [430310011](#)
Terminal, Male,
with 0.38µm Select
Gold (Au) Plated
Phosphor Bronze
Contact, 26-30 AWG,
Bag
Micro-Fit 3.0 Crimp [430310012](#)
Terminal, Male,
with 0.76µm Select
Gold (Au) Plated
Phosphor Bronze
Contact, 26-30 AWG,
Bag
Micro-Fit 3.0 Crimp [430310021](#)
Terminal, Male,
with Tin (Sn)
Plated Phosphor
Bronze Contact,
18 AWG, .073in /
1.85mm Max
Insulation Outside
Diameter, Reel
Micro-Fit 3.0 [430310022](#)
Crimp Terminal,
Male, with 0.38µm
Select Gold (Au)
Plated Phosphor
Bronze Contact,
18 AWG, .073in /
1.85mm Max
Insulation Outside
Diameter, Reel
Micro-Fit 3.0 [430310023](#)
Crimp Terminal,
Male, with 0.76µm
Select Gold (Au)
Plated Phosphor
Bronze Contact,
18 AWG, .073in /
1.85mm Max
Insulation Outside
Diameter, Reel
Micro-Fit TPA Crimp [430315003](#)
Terminal, Male, with
Tin (Sn) Pre-plated
Phosphor Bronze
Contact, 20-24 AWG,
Reel
Micro-Fit TPA Crimp [430315004](#)
Terminal, Male,
with 0.38µm Select
Gold (Au) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Reel

Micro-Fit TPA Crimp [430315005](#)
Terminal, Male,
with 0.76µm Select
Gold (Au) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Reel

Micro-Fit TPA Crimp [430315006](#)
Terminal, Male, with
2.54µm Matte Tin
Plated Phosphor
Bronze Contact,
20-24 AWG, Reel

Micro-Fit TPA Crimp [430315007](#)
Terminal, Male, with
Tin (Sn) Pre-plated
Phosphor Bronze
Contact, 26-30 AWG,
Reel

Micro-Fit TPA Crimp [430315008](#)
Terminal, Male,
with 0.38µm Select
Gold (Au) Plated
Phosphor Bronze
Contact, 26-30 AWG,
Reel

Micro-Fit TPA Crimp [430315009](#)
Terminal, Male,
with 0.76µm Select
Gold (Au) Plated
Phosphor Bronze
Contact, 26-30 AWG,
Reel

Micro-Fit TPA Crimp [430315010](#)
Terminal, Male, with
2.54µm Matte Tin
Plated Phosphor
Bronze Contact,
26-30 AWG, Reel

Micro-Fit 3.0 Crimp [457730001](#)
Terminal, Female,
with Lubricant, with
Tin (Sn) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Reel

Micro-Fit 3.0 Crimp [457730003](#)
Terminal, Female,
with Lubricant, with
Gold (Au) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Reel

Micro-Fit 3.0 Crimp [457730006](#)
Terminal, Female,
with Lubricant, with
Gold (Au) Plated
Phosphor Bronze
Contact, 26-30 AWG,
Reel

Micro-Fit 3.0 Crimp [457730053](#)
Terminal, Female,
with Lubricant, with
Gold (Au) Plated
Phosphor Bronze

	Contact, 20-24 AWG, Reel	
	Micro-Fit RMF Reduced Mating Force, Crimp Terminal, Female, with 0.38µm Selective Gold (Au) over Nickel (Ni), 20-24 AWG, without Lubricant	<u>462350001</u>
	Micro-Fit RMF Reduced Mating Force, Crimp Terminal, Female, with 0.76µm Selective Gold (Au) over Nickel (Ni), 20-24 AWG, without Lubricant	<u>462350002</u>
	Micro-Fit RMF Reduced Mating Force, Crimp Terminal, Female, with 0.38µm Selective Gold (Au) over Nickel (Ni), 26-30 AWG, without Lubricant	<u>462350003</u>
	Micro-Fit RMF Reduced Mating Force, Crimp Terminal, Female, with .0.76µm Selective Gold (Au) over Nickel (Ni), 26-30 AWG, without Lubricant	<u>462350004</u>
	Micro-Fit RMF High Mating Cycle, Reduced Mating Force, Crimp Terminal, Female, with 0.38µm Selective Gold (Au) over Nickel (Ni), 20-24 AWG, with Lubricant	<u>462355001</u>
	Micro-Fit RMF High Mating Cycle, Reduced Mating Force, Crimp Terminal, Female, with 0.76µm Selective Gold (Au) over Nickel (Ni), 20-24 AWG, with Lubricant	<u>462355002</u>
	Micro-Fit RMF High Mating Cycle, Reduced Mating Force, Crimp Terminal, Female, with 0.38µm Selective Gold (Au)	<u>462355003</u>

over Nickel (Ni), 26-30 AWG, with Lubricant Micro-Fit RMF	<u>462355004</u>
High Mating Cycle, Reduced Mating Force, Crimp Terminal, Female, with .076µm Selective Gold (Au) over Nickel (Ni), 26-30 AWG, with Lubricant	
1.25mm Pitch,	<u>500588000</u>
PicoBlade Female Crimp Terminal, Tin (Sn) Plating, 28-32 AWG, Reel	
1.25mm Pitch,	<u>500588100</u>
PicoBlade Female Crimp Terminal, Tin (Sn) Plating, 28-32 AWG, Bag	
1.25mm Pitch,	<u>500798000</u>
PicoBlade Female Crimp Terminal, Tin (Sn) Plating, 26-28 AWG, Reel	
1.25mm Pitch,	<u>500798100</u>
PicoBlade Female Crimp Terminal, Tin (Sn) Plating, 26-28 AWG, Bag	
1.25mm Pitch,	<u>501258000</u>
PicoBlade Male Crimp Terminal, Tin (Sn) Plating, 26-28 AWG, Reel	
1.25mm Pitch,	<u>501258100</u>
PicoBlade Male Crimp Terminal, Tin (Sn) Plating, 26-28 AWG, Bag	
1.25mm Pitch,	<u>501338000</u>
PicoBlade Male Crimp Terminal, Tin (Sn) Plating, 28-32 AWG, Reel	
1.25mm Pitch,	<u>501338100</u>
PicoBlade Male Crimp Terminal, Tin (Sn) Plating, 28-32 AWG, Bag	
2.00mm Pitch, Micro-	<u>502128000</u>
Latch Female Crimp Terminal, Tin (Sn) Plating, 24-30 AWG, Reel	
2.00mm Pitch, Micro-	<u>502128100</u>
Latch Female Crimp Terminal, Tin (Sn) Plating, 24-30 AWG, Bag	
2.00mm Pitch, Micro-	<u>503728000</u>
Latch Female Crimp	

Terminal, Tin (Sn) Plating, 22-26 AWG, Reel 2.00mm Pitch, Micro- <u>503728100</u> Latch Female Crimp Terminal, Tin (Sn) Plating, 22-26 AWG, Bag OBD-II Crimp <u>504208000</u> Terminal, Female, 50420, 4.00mm Pitch DuraClik Crimp <u>5600850101</u> Terminal, Female, 22-26 AWG, Reel

This document was generated on 08/17/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION