This document was generated on 08/25/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 1200310004

Status: Active

Overview: Brad Nano-Change (M8) Products

Description: Nano-Change (M8) Receptacle, 3 Poles, M8 x 0.5 Mounting Threads, Male (Straight) to 22 AWG Leads, 0.30m (11.81") Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

EU ELV
Not Relevant

EU RoHS
Compliant with Exemption 6(c)

China RoHS

REACH SVHC
Contained Per - D(2020)9139-DC (19 Jan 2021)
Lead

Halogen-Free Status
Not Low-Halogen

For more information, please visit Contact US

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
120031 Series

General	
Product Family	Industrial Receptacles
Series	120031
IP Rating	IP67
NEMA Rating	NEMA 6
Overview	Brad Nano-Change (M8) Products
Product Name	Nano-Change (M8)
Type	Single Ended (pigtail)
UPC	883906177775
Physical	
Coupling Type	External Thread
Gender	Male
Keyway	None
Length	0.30m
Material - Component	Nickel-plated Brass
Mounting Thread Size	M8 x 0.5
Net Weight	9.181/g
Orientation	Straight
Panel Mount	Front
Poles	3
Temperature Range - Operating	-25°C to +90°C
Wire Size AWG	24
Wire/Cable Type	Leads
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	60V AC / 75V DC
Material Info	
Engineering Number	4R3F06E02C3003
Reference - Drawing Numbers	
Sales Drawing	SD-120090-027-001

This document was generated on 08/25/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION