

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200680137](#)
Status: **Active**
Overview:
Description: Micro-Change (M12) Solid Body Splitter, 1 x 5-Pole Male to 2 x 5-Pole Females, Black Overmold

General

Product Family	Industrial Tees and Splitters
Series	120068
IP Rating	IP67
Overview	microchange_m12_connectors
Product Name	Micro-Change (M12)
Type	Splitter - Solid Body
UPC	78678872687

Physical

Drop Connector	Micro-Change (M12)
Drop Gender	Male
Keyway	Single
LED Indicator	No
Left Trunk Connector	Micro-Change (M12)
Left Trunk Gender	Female
Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Net Weight	30.000/g
Poles	5
Right Trunk Connector	Micro-Change (M12)
Right Trunk Gender	Female
Temperature Range - Operating	-25°C to +90°C

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	30V AC / 36V DC

Material Info

Engineering Number	0812-05EMF00001
--------------------	-----------------

Reference - Drawing Numbers

Sales Drawing	1200680137-000, SD-120068-031-001
---------------	-----------------------------------

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[120068](#) Series