This document was generated on 08/24/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 1200710039

Status: Active

Overview: Brad Micro-Change (M12) Connectors

Description: Micro-Change (M12) Single Keyway with PG9 Cable Fitting, Straight Male, 4 Poles, Cable Diameter 4.10-8.10mm



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR6837

General

Product Family	Field Attachable / Accessories
Series	120071
Approvals	cCSAus certified
IP Rating	IP67
Material - Contact	Brass
Overview	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (M12)
Type	Field Attachable Connector
UPC	78172553083

Physical

Cable Diameter	4.10 - 8.10mm (.161-.319")
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	Single
Material - Connector Body	PA
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Silver
Net Weight	0.062/lb
Orientation	Straight
Poles	4
Temperature Range - Operating	-25°C to +90°C
Wire Size AWG	18

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC / 300V DC

Material Info

Engineering Number	8A4006-32

Reference - Drawing Numbers

Sales Drawing	SD-130044-004-001

EU ELV
Not Relevant

EU RoHS
Compliant with Exemption 6(c)

China RoHS

REACH SVHC
Contained Per - D(2020)9139-DC (19 Jan 2021)
Lead

Halogen-Free Status
Not Low-Halogen

For more information, please visit Contact US

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
120071 Series

This document was generated on 08/24/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION