

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [1200845103](#)  
**Status:** **Active**  
**Overview:** [Brad Ultra-Lock Connection System](#)  
**Description:** Ultra-Lock (M12) Receptacle, 4 Poles, PG9 Mounting Threads, Male (Straight) to 0.34mm² PVC Leads, 0.30m (11.81") Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family Industrial Receptacles  
Series [120084](#)  
IP Rating IP69K  
NEMA Rating NEMA 6  
Overview [Brad Ultra-Lock Connection System](#)  
Product Name Ultra-Lock (M12)  
Type Single Ended (pigtail)  
UPC 883906778767

**Physical**

Coupling Type External Thread  
Gender Male  
Keyway Single  
Length 0.30m  
Material - Component Nickel-plated Brass  
Mounting Thread Size PG9  
Net Weight 10.000/g  
Orientation Straight  
Panel Mount Front  
Poles 4  
Temperature Range - Operating -25°C to +90°C  
Wire Size AWG 22  
Wire/Cable Type Leads, UL 1061

**Electrical**

Current - Maximum per Contact 4.0A  
Voltage - Maximum 250V AC/DC

**Material Info**

Engineering Number WR4J26E03C3003

**Reference - Drawing Numbers**

Sales Drawing SD-120084-023-001

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per -  
D(2020)9139-DC (19  
Jan 2021)  
Lead

**Halogen-Free  
Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

|                 |               |
|-----------------|---------------|
| China ROHS      | 50 Image      |
| ELV             | Not Relevant  |
| RoHS Phthalates | Not Contained |

**Search Parts in this Series**

[120084](#) Series