

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200895003](#)
Status: **Active**
Overview: [Brad Nano-Change \(M8\) Products](#)
Description: Y Nano-Change (M8) Splitter to Nano-Change (M8) 4 Pole Female to 4 Pole Male

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Industrial Tees and Splitters
Series [120089](#)
IP Rating IP67
Overview [Brad Nano-Change \(M8\) Products](#)
Product Name Nano-Change (M8)
Type Splitter - Solid Body
UPC 883906319472

Physical

Drop Connector Nano-Change (M8)
Drop Gender Male
Keyway None
Left Trunk Connector Nano-Change (M8)
Left Trunk Gender Female
Leg 1 Length N/A
Leg 2 Length N/A
Material - Cable Jacket N/A
Material - Connector Body PUR
Material - Coupling Nut Nickel-plated Brass
Net Weight 1.000/g
Poles 3
Right Trunk Connector Nano-Change (M8)
Right Trunk Gender Female
Temperature Range - Operating -20°C to +90°C

Electrical

Current - Maximum per Contact 4.0A
Voltage - Maximum 60V AC / 75V DC

Material Info

Engineering Number 0808 04LMF 00001

Reference - Drawing Numbers

Sales Drawing SD-120089-002

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS

ELV

RoHS Phthalates

50 Image

Not Relevant

Not Reviewed

Search Parts in this Series

[120089](#) Series