

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1201030003](#)
Status: **Active**
Overview: [PROFIBUS Solutions](#)
Description: PROFIBUS Attachable D-Sub Connector with Diagnostics LEDs and Programming Port, 45° Angle

Documents:
[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Field Attachable / Accessories
Series [120103](#)
IP Rating IP67
Material - Contact N/A
Overview [PROFIBUS Solutions](#)
Product Name D-Sub, PROFIBUS
Type Field Attachable Connector
UPC 78678899265

Physical
Cable Diameter N/A
Coupling Type D-Sub
Diagnostics / LEDs Yes
Diagnostics Port Yes
Gender N/A
Keyway None
Material - Connector Body Die-Cast Zinc
Material - Coupling Nut N/A
Material - Plating Mating n/a
Net Weight 89.811/g
Orientation 45° Angle
Poles N/A
Temperature Range - Operating -20°C to +80°C
Wire Size AWG N/A

Electrical
Current - Maximum per Contact 4.0A
Voltage - Maximum 30V

Material Info
Engineering Number PA9D0B-42

Reference - Drawing Numbers
Sales Drawing SD-120103-002



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[120103 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION