

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1202530527

Status:

Active

Overview:

Contrinex Inductive and Photoelectric

Description:

Contrinex Inductive Sensor, M5 Housing, 1.5mm Operating Distance, Embeddable, PNP, NO, 3-pin M8 Connector, 38mm Housing Length



Documents:

Product Specification 1202530527-000 (PDF)

RoHS Certificate of Compliance (PDF)

Datasheet (PDF)

General	
Product Family	Sensors
Series	120253
IP Rating	IP67
Overview	Contrinex Inductive and Photoelectric
Product Category	Sensors
Product Name	Contrinex
Type	Inductive
UPC	191130069224
Physical	
Connection	Connector (M8, 3-pin)
Length	38mm
Material - Housing	Stainless Steel
Material - Sensing Face	POM
Mounting Style	Embeddable
Net Weight	444.000/g
Operating Distance	1.5mm
Output	NO
Sensor Housing Size	M5
Temperature Range - Operating	-25° to +70°C
Electrical	
Polarity	PNP
Switching Frequency	≤ 3000 Hz
Material Info	
Engineering Number	DW-AS-623-M5
Reference - Drawing Numbers	
Product Specification	1202530527-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

120253 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION