

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1202540151](#)
Status: **Active**
Overview: [Contrinex Inductive and Photoelectric](#)
Description: Contrinex Photoelectric Sensor, M18 Housing, Reflex, PNP, Dark-ON, 2m 3-wire PVC Cable, 50mm Housing Length

Documents:
[Product Specification 1202540151-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General	
Product Family	Sensors
Series	120254
IP Rating	IP67
Operating Principle	Reflex
Overview	Contrinex Inductive and Photoelectric
Product Category	Sensors
Product Name	Contrinex
Type	Photoelectric
UPC	191130069170
Physical	
Connection	Cable (PVC 2m, 3-wire)
Length	50mm
Material - Housing	Chrome Plated Brass
Material - Window	Glass
Output	Dark-ON
Sensor Housing Size	M18
Temperature Range - Operating	-25° to +55°C
Electrical	
Polarity	PNP
Switching Frequency	≤ 1000 Hz
Material Info	
Engineering Number	LRK-1180-304
Reference - Drawing Numbers	
Product Specification	1202540151-000



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant with Exemption 6(c) REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[120254](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION