

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 1210120013

Status: **Active**

Overview:

Description: mPm DIN Base, Form A-18mm, B20 Base, 2 Pole Plus Ground Terminal, 250V AC/300V DC. Black. Nitrile Gasket with Screw

General

Product Family	Field Attachable / Accessories
Series	<u>121012</u>
Form	A - 18mm
IP Rating	IP65, IP67
Material - Contact	Brass
Overview	mpm_connectors
Product Name	mPm
Type	Field Attachable Connector
UPC	883906270476

Physical

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Polypropylene
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	9.400/g
Orientation	Straight
Pitch - Mating Interface	18.00mm
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	250V AC / 300V DC

Material Info

Engineering Number B202000N2

Reference - Drawing Numbers

Packaging Specification	PK-121012-B20-001
Product Specification	STR-1467-001
Sales Drawing	SD-121012-013-001

EU ELV

Not Relevant

EU RoHS

**Compliant with
Exemption 6(c)**

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)
Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

121012 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION