

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1210120112](#)  
**Status:** **Active**  
**Overview:**  
**Description:** mPm DIN Base, Form A-18mm, B30 Base, 2 Pole Plus Ground Terminal, 250V AC/300V DC, Black, Nitrile Gasket

**General**

Product Family	Field Attachable / Accessories
Series	<a href="#">121012</a>
Form	A - 18mm
IP Rating	IP65, IP67
Material - Contact	Brass
Overview	mpm_connectors
Product Name	mPm
Type	Field Attachable Connector
UPC	883906334659

**Physical**

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Polypropylene
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Orientation	Straight
Pitch - Mating Interface	18.00mm
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	N/A

**Electrical**

Current - Maximum per Contact	16.0A
Voltage - Maximum	250V AC / 300V DC

**Material Info**

Engineering Number	B302000N0
--------------------	-----------

**Reference - Drawing Numbers**

Packaging Specification	PK-121012-B30-001
Sales Drawing	SD-121012-112-001

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

Lead

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[121012 Series](#)