

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1212070082

Status:

Active

Overview:

mPm DIN Valve Connectors

Description:

mPm DIN Valve Connector, Form A-18mm, External Threads, 2 Pole Plus Ground with C3 Circuit, 12V, Red LED, Transparent, Nitrile Gasket

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Packaging Specification PK-121207-S28-001 (PDF)

Agency Certification	
UL	E218123
General	
Product Family	Field Attachable / Accessories
Series	121207
Form	A - 18mm
IP Rating	IP65, IP67
Material - Contact	Brass
Overview	mPm DIN Valve Connectors
Product Name	mPm
Type	Field Attachable Connector
UPC	884982502680
Physical	
Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	Yes
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Polyamide
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	19.911/g
Orientation	90° Angle
Pitch - Mating Interface	18.00mm
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	16.0A
Voltage - Maximum	12V
Material Info	
Engineering Number	S28200TC310R
Reference - Drawing Numbers	
Packaging Specification	PK-121207-S28-001
Sales Drawing	SD-121207-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2020)9139-DC (19 Jan 2021)

lead

Halogen-Free

Status

Low-Halogen

For more information, please visit Contact US

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

121207 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION