

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1212100032](#)
Status: **Active**
Overview: mPm DIN Valve Connectors
Description: mPm DIN Valve Connector, Form C-8mm, External Threads, 2 Pole Plus Ground with C4 Circuit, 24V, Red LED, Transparent, Nitrile Gasket

Documents:

Drawing (PDF)	Packaging Specification PK-121210-S25-001 (PDF)
Product Specification PS-121201-001-001 (PDF)	Test Summary STR-1299-001 (PDF)
Product Specification STR-1251-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Field Attachable / Accessories
Series	121210
Form	C - 8mm
IP Rating	IP65, IP67
Material - Contact	Brass
Overview	mPm DIN Valve Connectors
Product Name	mPm
Type	Field Attachable Connector
UPC	884982538757

Physical

Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	Yes
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Polyamide
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	9.789/g
Orientation	90° Angle
Pitch - Mating Interface	8.00mm
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	24V

Material Info

Engineering Number	S25200TC420T
--------------------	--------------

Reference - Drawing Numbers

Packaging Specification	PK-121210-S25-001
Product Specification	PS-121201-001-001, STR-1251-001
Sales Drawing	SD-121210-001
Test Summary	STR-1299-001



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Reviewed

RoHS Phthalates

Not Contained

Search Parts in this Series

[121210 Series](#)