
This document was generated on 07/31/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 1300250071
Status: Active
Overview: Brad Mini-Change Connectors
Description: Mini-Change Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 15 and 18 AWG, DeviceNet Thick (Trunk) Cable, 4.0m (13.12') Length



Series image - Reference only

Documents:
Drawing (PDF)
RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR6837
UL	E152210

General

Product Family	Industrial Cordsets
Series	130025
Connector End A	Mini-Change
Connector End B	Mini-Change
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Mini-Change Connectors
Product Name	DeviceNet Trunk, Mini-Change
Region	Europe
Type	Double Ended
UPC	78678829132

Physical

Cable Diameter	12.10mm (.480")
Cable Length	4.0m (13.12')
Color - Cable Jacket	Gray
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Coupling Nut	Die-Cast Zinc
Material - Plating Mating	Gold
Net Weight	793.709/g
Orientation	Straight to Straight
Poles	5
Temperature Range - Operating	-20°C to +80°C
Wire Size AWG	15, 18
Wire/Cable Type	N/A

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	300V AC/DC

Material Info

Engineering Number	DN11A-M040

Reference - Drawing Numbers

Sales Drawing	1300250051-000, SD-130025-001-001

EU ELV
Not Relevant

EU RoHS
Compliant with Exemption 6(c)

China RoHS

REACH SVHC
Contained Per - D(2020)9139-DC (19 Jan 2021)
Lead

Halogen-Free Status
Not Low-Halogen

For more information, please visit Contact US

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
130025 Series

This document was generated on 07/31/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION