

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300340005

Status:

Active

Overview:

Brad Mini-Change Connectors

Description:

Mini-Change Trunk Connector, Threaded, Single Keyway, Straight Female, 5 Poles



Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Agency Certification	
CSA	LR6837
General	
Product Family	Field Attachable / Accessories
Series	130034
Approvals	cCSAus certified
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Mini-Change Connectors
Product Name	Mini-Change
Type	Field Attachable Connector
UPC	78172553489
Physical	
Cable Diameter	5.00-12.00mm (.20-.48")
Coupling Type	Internal Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Female
Keyway	Single
Material - Connector Body	Polyamide
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	n/a
Net Weight	211.000/g
Orientation	Straight
Poles	5
Temperature Range - Operating	-25°C to +90°C
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	36V
Material Info	
Engineering Number	1A5000-34DN
Reference - Drawing Numbers	
Sales Drawing	SD-130034-003-001

EU ELV
Not Relevant

EU RoHS
Compliant with
Exemption 6(c)
REACH SVHC
Contained Per -
D(2020)9139-DC (19
Jan 2021)
Lead
Halogen-Free
Status
Not Low-Halogen

China RoHS

50 Image
Not Relevant
Not Contained

For more information, please visit [Contact US](#)

Search Parts in this Series

130034 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION