

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300350090](#)
Status: **Active**
Overview: [DeviceNet Solutions](#)
Description: DeviceNet Trunk Micro-Change Tee, 5 Poles, Male/Female with Female Drop, Nickel Plated Brass

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Industrial Tees and Splitters
Series [130035](#)
IP Rating IP67
Overview [DeviceNet Solutions](#)
Product Name DeviceNet Trunk
Type Drop Tee
UPC 78172553718

Physical
Color - Cable Jacket Gray
Drop Connector Micro-Change (M12)
Drop Gender Female
Keyway Single
LED Indicator No
Left Trunk Connector Micro-Change (M12)
Left Trunk Gender Female
Leg 1 Length N/A
Leg 2 Length N/A
Length 0.0559m
Material - Cable Jacket N/A
Material - Connector Body PUR
Material - Coupling Nut Nickel-plated Brass
Net Weight 35.440/g
Poles 5
Right Trunk Connector Micro-Change (M12)
Right Trunk Gender Male
Temperature Range - Operating -20°C to +80°C

Electrical
Current - Maximum per Contact 4.0A
Voltage - Maximum 250V

Material Info
Engineering Number MICT555

Reference - Drawing Numbers
Sales Drawing SD-130035-001-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2020)9139-DC (19 Jan 2021)	
Lead	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[130035](#) Series