

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300390300

Status:

Active

Overview:

Brad Mini-Change Connectors

Description:

DeviceNet Trunk Receptacle, 5 Poles, 1/2" - 14 NPT, Male (Straight) to Leads, 2.0m (6.56') Length



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR6837
UL	E152210
General	
Product Family	Industrial Receptacles
Series	130039
IP Rating	IP67
NEMA Rating	NEMA 6
Overview	Brad Mini-Change Connectors
Product Name	DeviceNet Trunk
Type	Single Ended (pigtail)
UPC	78678829667
Physical	
Coupling Type	External Thread
Gender	Male
Keyway	Single
Length	2.0m
Material - Component	Gray Anodized Aluminum
Mounting Thread Size	1/2" - 14 NPT
Net Weight	21.000/g
Orientation	Straight
Panel Mount	N/A
Poles	5
Temperature Range - Operating	-20°C to +80°C
Wire Size AWG	18
Wire/Cable Type	Thick Standard Cable
Electrical	
Current - Maximum per Contact	8.0A
Voltage - Maximum	300V AC/DC
Material Info	
Engineering Number	DN5100-M020
Reference - Drawing Numbers	
Sales Drawing	SD-130039-001-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c),6(b)	
REACH SVHC	
Not Contained Per - ED/108/2014 (17 Dec 2014)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

130039 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION