This document was generated on 08/13/2021


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 1300540010

Status: Active

Overview: Brad Industrial Ethernet Solutions

Description: Micro-Change (M12) 4 Pole, 90° D-Coded Adapter Female to Female RJ45, M16 x 1.5 Back Panel Mount



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family	Industrial Receptacles
Series	130054
IP Rating	IP67
Overview	Brad Industrial Ethernet Solutions
Product Name	Micro-Change (M12)
Type	Adapter
UPC	78678804544

Physical

Coupling Type	Internal Thread
Gender	Female
Keyway	D-coded
Length	0.0462m
Material - Component	Nylon
Mounting Thread Size	M16
Net Weight	0.053/kg
Orientation	90° to Straight
Panel Mount	Back
Poles	N/A
Temperature Range - Operating	-5°C to +60°C
Wire Size AWG	N/A
Wire/Cable Type	N/A

Electrical

Current - Maximum per Contact	N/A
Voltage - Maximum	N/A

Material Info

Engineering Number	ER1PADAPTER90

Reference - Drawing Numbers

Sales Drawing	SD-120109-010-001

EU ELV
Not Relevant

EU RoHS
Compliant with Exemption 6(c)

China RoHS

REACH SVHC
Not Reviewed

Halogen-Free Status
Not Reviewed

For more information, please visit Contact US

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
130054 Series

This document was generated on 08/13/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION