

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300600066](#)
Status: **Active**
Overview: [Brad Mini-Change Connectors](#)
Description: Mini-Change 4 Pole, 8 Ports Drop DeviceNet Aux Power

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E152210

General

Product Family Passive Distribution Boxes
 Series [130060](#)
 IP Rating IP67
 Overview [Brad Mini-Change Connectors](#)
 Product Name DeviceNet, Mini-Change
 UPC 78172501462

Physical

Bus I/O Mini-Change
 Cable Connector Orientation N/A
 Cable Length N/A
 Home Run Cable Length N/A
 Home Run Connector Mini-Change - 4 pole
 Home Run Interface Integrated Connector
 Keyway Single
 LED Indicator No
 Material - Cable Jacket N/A
 Material - Housing PBT
 Material - Metal Copper
 Material - Plating Mating Gold
 Net Weight 555.000/g
 Orientation Side Mount
 Poles 4
 Poles (wired) 4
 Ports 8
 Temperature Range - Operating 0°C to +60°C
 Wiring Configuration Single I/O per Port

Electrical


Current - Maximum per Contact 10.0A
 Functional Wiring Parallel
 Voltage - Maximum 600V AC/DC

Material Info

Engineering Number DNAUX8000

Reference - Drawing Numbers

Sales Drawing SD-130060-011-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Compliant

REACH SVHC

Not Contained Per
 -ED/01/2018 (15
 January 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Contained: alat

Search Parts in this Series

[130060 Series](#)