

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300700020](#)
Status: **Active**
Overview: [BradPower Cordsets and Receptacles](#)
Description: BradPower D-Size (1 3/8"–M35) Locking Clip, 44.96mm Diameter

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Field Attachable / Accessories
Series	130070
IP Rating	N/A
Material - Contact	N/A
Overview	BradPower Cordsets and Receptacles
Product Name	BradPower D-Size
Type	Accessory - Locking Clip
UPC	78678882759

Physical

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	N/A
Keyway	N/A
Material - Connector Body	Polyester
Material - Coupling Nut	N/A
Material - Plating Mating	n/a
Net Weight	127.721/g
Orientation	N/A
Poles	N/A
Temperature Range - Operating	-20°C to +90°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	N/A
Voltage - Maximum	N/A

Material Info

Engineering Number	66200A-10
--------------------	-----------

Reference - Drawing Numbers

Sales Drawing	SD-130070-003-001
---------------	-------------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[130070 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION