This document was generated on 08/24/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 1300700024
Status: Active
Overview: BradPower Cordsets and Receptacles
Description: BradPower D-Size (1 3/8"–M35) Male Field Attachable, 4-Pole, Straight



Series image - Reference only

Documents:
Drawing (PDF)
RoHS Certificate of Compliance (PDF)

Agency Certification

UL	E258922

General

Product Family	Field Attachable / Accessories
Series	130070
Application	Power
Approvals	UL Listed: E258922
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	BradPower Cordsets and Receptacles
Product Name	BradPower D-Size
Type	Field Attachable Connector
UPC	78678804606

Physical

Cable Diameter	11.00-21.00mm (.43-.82")
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	Single
Material - Connector Body	Nylon
Material - Coupling Nut	Anodized Aluminum
Material - Plating Mating	Gold
Net Weight	141.520/g
Orientation	Straight
Poles	4
Temperature Range - Operating	-20°C to +90°C
Wire Size AWG	10, 12, 14, 8

Electrical

Current - Maximum per Contact	32.0A
Voltage - Maximum	600V AC/DC

Material Info

Engineering Number	CA4006-39

Reference - Drawing Numbers

Sales Drawing	SD-120336-002-001

EU ELV
Not Relevant

EU RoHS
Compliant with Exemption 6(c)

China RoHS

REACH SVHC
Not Reviewed

Halogen-Free Status
Not Low-Halogen

For more information, please visit Contact US

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
130070 Series

This document was generated on 08/24/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION