

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1501700003

Status:

Active

Overview:

Ditto Wire-to-Wire Interconnects

Description:

Ditto Hermaphroditic Crimp Housing, Positive Lock, 3 Circuit

Documents:

- 3D Model

Packaging Specification PK-150170-0000-000 (PDF)
- Drawing (PDF)

Test Summary TS-150170-0000-001 (PDF)
- 3D Model (PDF)

Datasheet (PDF)
- Product Specification PS-150170-0000-001 (PDF)

RoHS Certificate of Compliance (PDF)
- Application Specification 1501700000-AS-000 (PDF)

General

Product Family

Crimp Housings

Series

150170

Application

Power, Wire-to-Wire

Overview

Ditto Wire-to-Wire Interconnects

Product Name

Ditto

UPC

889056215671

Physical

Circuits (maximum)

3

Color - Resin

Natural (White)

Gender

Hermaphroditic

Glow-Wire Capable

No

Lock to Mating Part

Yes

Material - Resin

Nylon

Net Weight

0.948/g

Number of Rows

1

Packaging Type

Bag

Panel Mount

No

Pitch - Mating Interface

3.00mm

Pitch - Termination Interface

3.00mm

Temperature Range - Operating

-40° to +105°C, -40° to +80°C, See Product Specification

Material Info

Reference - Drawing Numbers

Application Specification

1501700000-AS-000

Packaging Specification

PK-150170-0000-000

Product Specification

PS-150170-0000-001

Sales Drawing

SD-150170-0000-000

Test Summary

TS-150170-0000-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

150170 Series

Mates With

Ditto Hermaphroditic Crimp Housing [150170](#)

Use With

Ditto Hermaphroditic Terminals [150200](#)

Ditto TPA Retainer [150212](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION