

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0015060041

Status:

Active

Overview:

Mini-Fit Family Power Connectors

Description:

Mini-Fit BMI Receptacle Housing, 4.20mm Pitch, Dual Row with Panel Mount Ears, PA Polyamide Nylon 6/6, UL 94V-0, 4 Circuits

Documents:

- 3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification 55560002-PS-CH-000 (PDF)

Product Specification 55560002-PS-ES-000 (PDF)

Product Specification 55560002-PS-SK-000 (PDF)
- Product Specification PS-45750-001-001 (PDF)

Product Specification PS-5556-002-001 (PDF)

Packaging Specification PK-42474-001-001 (PDF)

Test Summary TS-5556-002-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

UL

LR19980

E29179

General

Product Family

Series

Application

Comments

Crimp Housings

42474

Power, Wire-to-Board, Wire-to-Wire

Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 series terminals crimped to 16 AWG wire. . See Molex product specification PS-45750-001 for additional current derating information.

Overview

Product Name

UPC

Mini-Fit Family Power Connectors

Mini-Fit BMI

800753641129

Physical

Breakaway

Circuits (maximum)

Color - Resin

Flammability

Gender

Glow-Wire Capable

Lock to Mating Part

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Stackable

Temperature Range - Operating

No

4

Natural (White)

94V-0

Receptacle

No

None

Nylon

3.360/g

2

Bag

Yes

4.20mm

4.20mm

Yes

No

-40° to +105°C

Electrical

Current - Maximum per Contact

13.0A

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Engineering Number

42474-0421



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

42474 Series

Mates With

42475 MiniFit BMI Plug Housing. 43879 MiniFit CPI Header. MiniFit BMI Header 42404 , 42440. MiniFit SMC Surface Mount Compatible Header 43810 , 44068

Use With

Mini-Fit Female Crimp Terminals 5556

Mini-Fit Plus HCS Crimp Terminal 45750
Mini-Fit Pre-Crimped Leads 797580001 , 797580009

Reference - Drawing Numbers

Packaging Specification	PK-42474-001-001
Product Specification	55560002-PS-CH-000, 55560002-PS-ES-000, 55560002-PS-SK-000, PS-45750-001-001, PS-5556-002-001
Sales Drawing	SD-42474-XXXX-001
Test Summary	TS-5556-002-001

This document was generated on 08/16/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION