

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1726722006](#)
Status: **Active**
Overview: Super Sabre Connector System
Description: 7.50mm Pitch Super Sabre Receptacle Crimp Housing, UL 94V-0, 6 Circuits

Documents:
[3D Model \(PDF\)](#) [Packaging Specification PK-44441-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [Test Summary TS-171825-001-001 \(PDF\)](#)
[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-171825-001-001 \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family Crimp Housings
Series [172672](#)
Application Power, Wire-to-Board, Wire-to-Wire
Overview [Super Sabre Connector System](#)
Product Name Super Sabre
UPC 889056025836

Physical

Circuits (maximum) 6
Color - Resin Black
Flammability 94V-0
Gender Receptacle
Glow-Wire Capable No
Keying to Mating Part Yes
Lock to Mating Part Yes
Material - Resin Nylon
Net Weight 4.700/g
Number of Rows 1
Packaging Type Carton
Panel Mount No
Pitch - Mating Interface 7.50mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -40° to +125°C

Electrical

Current - Maximum per Contact 34.0A

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers

Packaging Specification PK-44441-001-001
Product Specification PS-171825-001-001
Sales Drawing 1726720000-SD-000
Test Summary TS-171825-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[172672](#) Series

Mates With

Super Sabre Vertical Header [172042](#) .
Super Sabre Right Angle Header [172043](#) .
Super Sabre Plug Housing [172673](#) , [43680](#)

Use With

[171825](#) Super Sabre Female Crimp
Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION