

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1729531401

Status:

Active

Overview:

Micro-Fit Connector System

Description:

Micro-Fit Terminal Position Assurance (TPA) Retainer, 14 Circuits, 3.00mm Pitch, UL 94V-0, Low-Halogen, Natural



Series image - Reference only

Documents:

- Drawing (PDF)

3D Model

3D Model (PDF)

Product Specification 430450001-PS-KO-000 (PDF)

Product Specification 430450001-PS-SP-000 (PDF)

Product Specification PS-43045-001 (PDF)
- Packaging Specification 1729530001-PK-000 (PDF)

Test Summary TS-43045-001-001 (PDF)

Test Summary TS-43045-002-001 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family	Accessories
Series	172953
Comments	See Product Specification for maximum current rating by circuit size and wire AWG
Component Type	Terminal Position Assurance
Overview	Micro-Fit Connector System
Product Name	Micro-Fit TPA
UPC	889056430128

Physical

Circuits (Loaded)	14
Circuits (maximum)	14
Color - Resin	Natural
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.164/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Packaging Specification	1729530001-PK-000
Product Specification	430450001-PS-KO-000, 430450001-PS-SP-000, PS-43045-001
Sales Drawing	SD-172953-001-001
Test Summary	TS-43045-001-001, TS-43045-002-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

172953 Series

Use With

Micro-Fit TPA Receptacle Housing Low-Halogen 172952
 Micro-Fit TPA Plug Housing 203632

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION