



RoHS compliant

No.	St.	Part	Type Description/Material	Surface plating/Colour/Class
3	5	Signal contact	P0 / Brass	0.8µm Au / AWG 20
2	1	Shell	Steel	tin plated
1	1	Insulator	PBT (-55°C - +130°C)	green

Measurement without tolerance occ. to ISO 2768-m	SCALE 2:1	TITLE
NAME / DATE		D-Sub Mixed-Layout Connector
DRAWN Denzinger 19-03-2003		
CHECKED Floßmann 19-03-2003		



DWG.NO.	REV.
FM7W2P-K120	1

1	REV.	DATE	CH.-NO.	ORIGINAL: DIN A3-DRAWING AS A FILE	REPLACEMENT FOR:	PAGES 1
---	------	------	---------	------------------------------------	------------------	---------

COMMENT: ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT, IT MAY NEITHER BE DUBLICATED NOR MADE AVAILABLE TO A THIRD PARTY. AND IT ALSO MAY NOT BE IMPROPERLY USED BY THE RECEIVER, OR A THIRD PARTY.