

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1731090082

Status:

Active

Overview:

FCT D-Sub Connectors

Description:

FCT Standard-Density D-Sub Connector, Male, Straight, Solder Cup, Gold Plating, 200 Mating Cycles, 50 Circuits

Documents:

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

Brochure (PDF)

General

Product Family

D-Sub Products

Series

173109

IP Rating

IP20

Overview

FCT D-Sub Connectors

Product Category

D-Sub Connector

Product Name

FCT Products

Type

Standard Density

UPC

889056485647

Physical

Circuits (Loaded)

50

Circuits (maximum)

50

Color - Resin

White

Durability (mating cycles max)

200

Gender

Male

Material - Contact

Copper Alloy

Material - Resin

PBT

Material - Shell

Steel

Net Weight

17.100/g

Number of Rows

3

Orientation

Straight

PCB Locator

No

PCB Retention

None

Packaging Type

Carton

Panel Mount

Rear

Panel Mount Method

Flange

Pitch - Mating Interface

2.84mm

Pitch - Termination Interface

2.84mm

Plating - Contact

Gold over Nickel

Plating - Shell

Tin

Polarized to Mating Part

Yes

Ports

1

Shielded

Yes

Temperature Range - Operating

-55° to +125°C

Termination Style

Solder Cup

Waterproof / Dustproof

No

Waterproof / Dustproof Type

IP20

Wire Size AWG

20

Electrical

Current - Maximum per Contact

7.5A

Material Info

Engineering Number

F50P0G2



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

173109 Series

Mates With

FCT Standard-Density D-Sub, Size 5, 50 Position, Socket

This document was generated on 07/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION