


20:30:32

10



2

1

NOTES:

- 1. MATERIAL:
 - (A). SPADE TONGUE TERMINAL: COPPER
 - PLATING: ELECTRO-TIN (.0003 MIN.)
- (B). INSULATION: MOLDED PVC (YELLOW)
- 2. MWID: MAXIMUM WIRE INSULATION DIAMETER
- 3. WIRE SIZE: 12 -10 AWG
 - 4.0 -6.0 MM²
- 4. ALL DIMENSIONS IN INCHES/[MM].
- 5. PARTS ARE ROHS COMPLIANT.
- 6. DIMS. SHOWN ARE FOR REFERENCE ONLY.

| DOCUMENT STATUS | P1 | RELEASE DATE | 2019/08/05

SYMB	OLS	THIS DRAWING C		INS INFO					NOLOGIES, LLC AND SHO	OULD NOT BE US	SED WITH	HOUT WRI	TTEN PER	RMISSION
\ =	0	INCH/MM		TS	ECTR/NX		C: MIGRATIO	N IO		no	le	X		
E =	0	GENERAL TOLERANCES (UNLESS SPECIFIED)							=					
=	0	MM INCH			EC NO:	EC NO: 620815			SPADE TONGUE TERMINAL					
\S/ =	0	4 PLACES ±	± ±		DRWN:	DRWN: ABENJAMINLW 2019/07/01			INSULKRIMP 200-SERIES					
vananaa	_	3 PLACES ±		± .00:	CHK'D:	GROJAS	01	2019/07/18						
=	0	2 PLACES ±	0.13	± .01	APPR:	.PPR: JMACNEIL 2019/08/05			PRODUCT CUSTOMER DRAWING					
₹ =	0	1 PLACE ± 0.25 ±			INITIAL	INITIAL REVISION:			DOCUMENT NUMBER DOC TYPE DOC PART REVISION					REVISION
=	0	0 PLACES ±	± ±		DRWN:	DRWN: JJ			1012		DOD	000	_	
		ANGULAR TOL ± 0.5°			APPR:	APPR: JMACNEIL			19131		PSD	000	A	
= =	0	DRAFT WHERE APPLICABLE			THIRD ANGL	THIRD ANGLE PROJECTION		SERIES	MATERIAL NUMBER	'		SHEET NUMBER		
<u>~</u> =	0	MUST REMAIN WITHIN DIMENSIONS					C-SIZE	19131	SEE TABLE	GENERA	AL MARKET 1 OF)F 1	
	5			4			3	2	2		1			