

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0192030083

Status: **Active**

Overview:

Description: Krimptite Temp-Term Ring Tongue Terminal for 14 to 16 AWG Wire, Stud Size 8 (M4)

Agency Certification

UL E32244

General

Product Family	Ring and Spade Terminals
Series	<u>19203</u>
Comments	1200° F (649° C)
Crimp Quality Equipment	Yes
Overview	high_temperature_temp_terms_terminals
Product Name	Krimptite, Temp-Terms
Type	Ring
UPC	800755059397

Physical

Barrel Type	Closed
Insulation	None
Net Weight	0.628/g
Packaging Type	Bag
Stud Size	8 (M4)
Wire Size AWG	14, 16
Wire Size mm ²	1.00-2.50

Material Info

Engineering Number BB-U-137-08

Reference - Drawing Numbers

Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	192030077-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

19203 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade	<u>640030100</u>
Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm ² - 0.5mm ²	
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640070100</u>
ServiceGrade Hand Crimp Tool - Ratchet	<u>640160038</u>

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION