

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0193230009](#)
Status: **Active**
Overview: [Metric Ring Terminals](#)
Description: VersaKrimp Metric Ring Terminal for M5 Stud Size (#10), Un-insulated

Documents:

[3D Model](#) [Drawing \(PDF\)](#)
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E32244

General

Product Family Ring and Spade Terminals
 Series [19323](#)
 Crimp Quality Equipment Yes
 Overview [Metric Ring Terminals](#)
 Product Name VersaKrimp
 Type Ring
 UPC 887191289939

Physical

Barrel Type Closed - Brazed
 Insulation None
 Material - Metal Copper Alloy
 Material - Plating Mating Tin
 Net Weight 0.699/g
 Packaging Type Bag
 Stud Size M5
 Wire Size AWG N/A

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Engineering Number BB2,5-339-M5

Reference - Drawing Numbers

Sales Drawing SD-19323-001-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2020)9139-DC (19
 Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[19323 Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm ² - 0.5mm ²	640030100
Crimp Head for the AT-200 Pneumatic Hand Tool	640070100
ServiceGrade Hand Crimp Tool - Ratchet	640160038

This document was generated on 08/23/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION